

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262737

Luminaire Tested: P3A13R409727DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409727DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1139.0 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262737

CATALOG NUMBER: P3A13R409727DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1262737

CATALOG NUMBER: P3A13R409727DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	580568
5°	576380
10°	561290
15°	501388
20°	332459
25°	124556
30°	33322
35°	13010
40°	4666
45°	2233
50°	682
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2233 cd/sqm

TEST NUMBER: P1262737
 CATALOG NUMBER: P3A13R409727DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.1	21.7
10°-20°	585.2	51.4
20°-30°	265.4	23.3
30°-40°	34.4	3.0
40°-50°	6.0	0.5
50°-60°	0.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.7	96.4
0°-40°	1132.1	99.4
0°-60°	1138.8	100.0
0°-90°	1139.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2648	
5°	2618	247
15°	2209	585
25°	515	265
35°	49	34
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1262737

CATALOG NUMBER: P3A13R409727DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2647.6
1°	2646.0
2°	2642.0
3°	2636.1
4°	2628.5
5°	2618.5
6°	2607.0
7°	2592.6
8°	2575.1
9°	2551.1
10°	2520.8
11°	2485.3
12°	2437.9
13°	2379.3
14°	2302.7
15°	2208.6
16°	2088.6
17°	1951.8
18°	1787.6
19°	1614.1
20°	1424.7
21°	1235.3
22°	1048.7
23°	862.9
24°	680.2
25°	514.8
26°	381.2
27°	279.1
28°	209.7
29°	163.1
30°	131.6
31°	108.9
32°	90.9
32.5°	82.9
33°	75.0
34°	61.0
35°	48.6
36°	38.3
37°	30.3
37.5°	27.1
38°	23.9
39°	19.9
40°	16.3
42.5°	10.8
45°	7.2

TEST NUMBER: P1262737

CATALOG NUMBER: P3A13R409727DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.4
50°	2.0
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)