

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265852

Luminaire Tested: P3A20R409730D010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265852  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R409730D010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1354.0 lumens  
Efficiency: N/A  
Efficacy: 47.0 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265852

CATALOG NUMBER: P3A20R409730D010 E3DLD1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1265852

CATALOG NUMBER: P3A20R409730D010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 83  |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 75  | 72  |  | 78  |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  |  | 75  | 70  | 66  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  |  | 70  | 65  | 61  |  | 68  |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  |  | 62  | 56  | 53  |  | 61  |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 57  |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 303945 |
| 5°  | 298436 |
| 10° | 281313 |
| 15° | 255507 |
| 20° | 224463 |
| 25° | 191697 |
| 30° | 158809 |
| 35° | 122469 |
| 40° | 87163  |
| 45° | 58735  |
| 50° | 32033  |
| 55° | 22594  |
| 60° | 21270  |
| 65° | 19665  |
| 70° | 17503  |
| 75° | 16691  |
| 80° | 13386  |
| 85° | 11322  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 58735 cd/sqm

TEST NUMBER: P1265852

CATALOG NUMBER: P3A20R409730D010 E3DLD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 126.4  | 9.3       |
| 10°-20°   | 313.5  | 23.2      |
| 20°-30°   | 362.5  | 26.8      |
| 30°-40°   | 285.7  | 21.1      |
| 40°-50°   | 146.6  | 10.8      |
| 50°-60°   | 56.1   | 4.1       |
| 60°-70°   | 37.1   | 2.7       |
| 70°-80°   | 20.2   | 1.5       |
| 80°-90°   | 6.0    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 802.4  | 59.3      |
| 0°-40°    | 1088.1 | 80.4      |
| 0°-60°    | 1290.8 | 95.3      |
| 0°-90°    | 1354.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1354.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1386 |      |
| 5°  | 1356 | 126  |
| 15° | 1126 | 314  |
| 25° | 792  | 362  |
| 35° | 458  | 286  |
| 45° | 189  | 147  |
| 55° | 59   | 56   |
| 65° | 38   | 37   |
| 75° | 20   | 20   |
| 85° | 4    | 6    |
| 90° | 0    |      |

TEST NUMBER: P1265852

CATALOG NUMBER: P3A20R409730D010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1386.1 |
| 2.5°  | 1378.5 |
| 5°    | 1355.8 |
| 7.5°  | 1316.4 |
| 10°   | 1263.4 |
| 12.5° | 1201.3 |
| 15°   | 1125.5 |
| 17.5° | 1046.8 |
| 20°   | 961.9  |
| 22.5° | 875.6  |
| 25°   | 792.3  |
| 27.5° | 709.0  |
| 30°   | 627.2  |
| 32.5° | 543.8  |
| 35°   | 457.5  |
| 37.5° | 377.2  |
| 40°   | 304.5  |
| 42.5° | 242.4  |
| 45°   | 189.4  |
| 47.5° | 137.9  |
| 50°   | 93.9   |
| 52.5° | 68.2   |
| 55°   | 59.1   |
| 57.5° | 53.0   |
| 60°   | 48.5   |
| 62.5° | 42.4   |
| 65°   | 37.9   |
| 67.5° | 31.8   |
| 70°   | 27.3   |
| 72.5° | 22.7   |
| 75°   | 19.7   |
| 77.5° | 15.1   |
| 80°   | 10.6   |
| 82.5° | 9.1    |
| 85°   | 4.5    |
| 87.5° | 3.0    |
| 90°   | 0.0    |

(END OF REPORT)