

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266005

Luminaire Tested: P3A20R709730D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266005
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R709730D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1896.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266005
CATALOG NUMBER: P3A20R709730D010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1266005
 CATALOG NUMBER: P3A20R709730D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376483
5°	359255
10°	341811
15°	332669
20°	320395
25°	303211
30°	282018
35°	236908
40°	152686
45°	70953
50°	18626
55°	4626
60°	4649
65°	3943
70°	3911
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 70953 cd/sqm



TEST NUMBER: P1266005
 CATALOG NUMBER: P3A20R709730D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.8	8.1
10°-20°	411.8	21.7
20°-30°	575.3	30.3
30°-40°	533.4	28.1
40°-50°	191.2	10.1
50°-60°	16.2	0.9
60°-70°	8.1	0.4
70°-80°	5.2	0.3
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1139.8	60.1
0°-40°	1673.2	88.3
0°-60°	1880.7	99.2
0°-90°	1896.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1896.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1717	
5°	1632	153
15°	1465	412
25°	1253	575
35°	885	533
45°	229	191
55°	12	16
65°	8	8
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P1266005
CATALOG NUMBER: P3A20R709730D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1716.9
2.5°	1691.2
5°	1632.1
7.5°	1577.5
10°	1535.1
12.5°	1500.2
15°	1465.4
17.5°	1423.0
20°	1373.0
22.5°	1315.4
25°	1253.2
27.5°	1189.6
30°	1113.8
32.5°	1016.8
35°	885.0
37.5°	716.8
40°	533.4
42.5°	363.7
45°	228.8
47.5°	127.3
50°	54.6
52.5°	18.2
55°	12.1
57.5°	10.6
60°	10.6
62.5°	9.1
65°	7.6
67.5°	7.6
70°	6.1
72.5°	6.1
75°	4.5
77.5°	4.5
80°	3.0
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)