

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263722

Luminaire Tested: P3A02R109730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R109730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 123.0 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263722

CATALOG NUMBER: P3A02R109730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263722

CATALOG NUMBER: P3A02R109730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53044
5°	49020
10°	39144
15°	29557
20°	22519
25°	17154
30°	12280
35°	8031
40°	4924
45°	2977
50°	1979
55°	1529
60°	1316
65°	1141
70°	1026
75°	1017
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2977 cd/sqm

TEST NUMBER: P1263722

CATALOG NUMBER: P3A02R109730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.7	16.0
10°-20°	36.4	29.6
20°-30°	32.4	26.3
30°-40°	19.2	15.6
40°-50°	7.9	6.4
50°-60°	3.7	3.0
60°-70°	2.2	1.8
70°-80°	1.2	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.5	72.0
0°-40°	107.7	87.6
0°-60°	119.3	97.0
0°-90°	123.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	123.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	242	
5°	223	20
15°	130	36
25°	71	32
35°	30	19
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263722

CATALOG NUMBER: P3A02R109730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	241.9
1°	241.3
2°	239.5
3°	235.9
4°	229.9
5°	222.7
6°	214.9
7°	205.7
8°	196.1
9°	186.4
10°	175.8
12.5°	151.6
15°	130.2
17.5°	111.9
20°	96.5
22.5°	82.9
25°	70.9
27.5°	59.3
30°	48.5
32.5°	38.7
35°	30.0
37.5°	23.0
40°	17.2
42.5°	12.8
45°	9.6
47.5°	7.4
50°	5.8
52.5°	4.8
55°	4.0
57.5°	3.4
60°	3.0
62.5°	2.6
65°	2.2
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.2
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)