

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262936

Luminaire Tested: P3A17R159727DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R159727DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 548.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262936
CATALOG NUMBER: P3A17R159727DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1262936
 CATALOG NUMBER: P3A17R159727DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	468142
5°	415539
10°	288572
15°	170648
20°	97192
25°	55552
30°	30739
35°	16383
40°	9074
45°	4900
50°	3070
55°	2409
60°	2105
65°	1920
70°	1667
75°	1779
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4900 cd/sqm



TEST NUMBER: P1262936
 CATALOG NUMBER: P3A17R159727DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	29.3
10°-20°	211.9	38.7
20°-30°	109.1	19.9
30°-40°	40.9	7.5
40°-50°	13.4	2.4
50°-60°	5.8	1.1
60°-70°	3.7	0.7
70°-80°	2.1	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.5	87.9
0°-40°	522.4	95.3
0°-60°	541.6	98.8
0°-90°	548.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	548.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2135	
5°	1888	161
15°	752	212
25°	230	109
35°	61	41
45°	16	13
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1262936
CATALOG NUMBER: P3A17R159727DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2134.9
1°	2130.6
2°	2102.7
3°	2049.3
4°	1979.1
5°	1887.8
6°	1784.3
7°	1670.8
8°	1544.7
9°	1420.1
10°	1296.0
12.5°	997.2
15°	751.7
17.5°	562.8
20°	416.5
22.5°	310.9
25°	229.6
27.5°	167.3
30°	121.4
32.5°	86.0
35°	61.2
37.5°	43.8
40°	31.7
42.5°	22.7
45°	15.8
47.5°	11.6
50°	9.0
52.5°	7.4
55°	6.3
57.5°	5.3
60°	4.8
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)