

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262987

Luminaire Tested: P3A17R259727DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R259727DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1372.1 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262987

CATALOG NUMBER: P3A17R259727DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1262987

CATALOG NUMBER: P3A17R259727DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	109	108		107	106	105		103	103	102		100	99	99
2	112	108	105	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	108	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	105	100	97	94		104	99	96	93		97	95	92		96	93	91		94	92	90
5	103	97	93	90		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	87		99	93	90	87		92	89	87		91	88	86		90	87	86
7	97	91	88	85		96	91	87	85		90	87	84		89	86	84		88	85	83
8	95	89	85	83		94	89	85	82		88	84	82		87	84	82		86	83	81
9	93	87	83	80		92	86	83	80		86	82	80		85	82	80		84	82	80
10	91	85	81	78		90	84	81	78		84	80	78		83	80	78		82	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1466856
5°	1360485
10°	1055068
15°	529038
20°	173802
25°	69101
30°	25928
35°	7495
40°	3406
45°	1333
50°	1092
55°	841
60°	965
65°	1141
70°	705
75°	932
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 1389 cd/sqm

TEST NUMBER: P1262987

CATALOG NUMBER: P3A17R259727DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	543.6	39.6
10°-20°	648.6	47.3
20°-30°	146.2	10.7
30°-40°	23.7	1.7
40°-50°	4.3	0.3
50°-60°	2.3	0.2
60°-70°	2.0	0.1
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1338.4	97.5
0°-40°	1362.1	99.3
0°-60°	1368.7	99.8
0°-90°	1372.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1372.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6689	
5°	6181	544
15°	2330	649
25°	286	146
35°	28	24
45°	4	4
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1262987

CATALOG NUMBER: P3A17R259727DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6689.4
1°	6678.7
2°	6624.8
3°	6525.6
4°	6375.8
5°	6180.7
6°	5947.9
7°	5695.6
8°	5406.7
9°	5090.9
10°	4738.4
11°	4332.1
12°	3864.3
13°	3374.9
14°	2850.0
15°	2330.4
17.5°	1328.0
20°	744.8
22.5°	449.5
25°	285.6
27.5°	175.7
30°	102.4
32.5°	53.9
35°	28.0
37.5°	18.3
40°	11.9
42.5°	7.5
45°	4.3
47.5°	3.2
50°	3.2
52.5°	3.2
55°	2.2
57.5°	2.2
60°	2.2
62.5°	2.2
65°	2.2
67.5°	2.2
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1262987

CATALOG NUMBER: P3A17R259727DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)