

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263043

Luminaire Tested: P3A17R309727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R309727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 695.0 lumens
Efficiency: N/A
Efficacy: 32.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263043
CATALOG NUMBER: P3A17R309727DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1263043

CATALOG NUMBER: P3A17R309727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237503
5°	230090
10°	207322
15°	171488
20°	132778
25°	99611
30°	72315
35°	48185
40°	29627
45°	17366
50°	10678
55°	8640
60°	7543
65°	6174
70°	5514
75°	5507
80°	4041
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17366 cd/sqm



TEST NUMBER: P1263043
 CATALOG NUMBER: P3A17R309727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	13.8
10°-20°	208.1	29.9
20°-30°	189.3	27.2
30°-40°	114.4	16.5
40°-50°	45.9	6.6
50°-60°	20.3	2.9
60°-70°	12.3	1.8
70°-80°	6.7	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.5	71.0
0°-40°	608.0	87.5
0°-60°	674.2	97.0
0°-90°	695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1083	
5°	1045	96
15°	755	208
25°	412	189
35°	180	114
45°	56	46
55°	23	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1263043
CATALOG NUMBER: P3A17R309727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1083.1
1°	1082.0
2°	1077.7
3°	1070.1
4°	1059.4
5°	1045.3
6°	1028.1
7°	1009.8
8°	986.1
9°	959.1
10°	931.1
11°	898.8
12°	864.3
13°	829.8
14°	792.1
15°	755.4
17.5°	659.5
20°	569.0
22.5°	485.0
25°	411.7
27.5°	344.9
30°	285.6
32.5°	230.6
35°	180.0
37.5°	137.9
40°	103.5
42.5°	75.4
45°	56.0
47.5°	42.0
50°	31.3
52.5°	24.8
55°	22.6
57.5°	19.4
60°	17.2
62.5°	14.0
65°	11.9
67.5°	10.8
70°	8.6
72.5°	7.5
75°	6.5
77.5°	5.4
80°	3.2
82.5°	2.2
85°	2.2
87.5°	1.1



TEST NUMBER: P1263043
CATALOG NUMBER: P3A17R309727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)