

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263070

Luminaire Tested: P3A17R359727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R359727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1133.0 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263070
CATALOG NUMBER: P3A17R359727DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1263070
 CATALOG NUMBER: P3A17R359727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	571445
5°	549195
10°	478504
15°	366495
20°	245208
25°	148363
30°	85152
35°	47596
40°	25305
45°	13025
50°	6243
55°	4932
60°	4736
65°	3891
70°	4167
75°	3643
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13025 cd/sqm



TEST NUMBER: P1263070
 CATALOG NUMBER: P3A17R359727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.0	20.0
10°-20°	439.9	38.8
20°-30°	288.0	25.4
30°-40°	116.8	10.3
40°-50°	35.0	3.1
50°-60°	11.9	1.1
60°-70°	8.0	0.7
70°-80°	4.7	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.9	84.3
0°-40°	1071.7	94.6
0°-60°	1118.7	98.7
0°-90°	1133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2606	
5°	2495	227
15°	1614	440
25°	613	288
35°	178	117
45°	42	35
55°	13	12
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1263070
CATALOG NUMBER: P3A17R359727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2606.0
1°	2601.6
2°	2589.8
3°	2566.1
4°	2538.1
5°	2495.0
6°	2441.1
7°	2380.7
8°	2312.8
9°	2235.2
10°	2149.0
11°	2053.1
12°	1952.9
13°	1840.8
14°	1734.1
15°	1614.4
17.5°	1324.5
20°	1050.8
22.5°	808.3
25°	613.2
27.5°	457.0
30°	336.3
32.5°	246.8
35°	177.8
37.5°	126.1
40°	88.4
42.5°	61.4
45°	42.0
47.5°	28.0
50°	18.3
52.5°	14.0
55°	12.9
57.5°	11.9
60°	10.8
62.5°	9.7
65°	7.5
67.5°	6.5
70°	6.5
72.5°	5.4
75°	4.3
77.5°	3.2
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1



TEST NUMBER: P1263070
CATALOG NUMBER: P3A17R359727DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)