

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263118

Luminaire Tested: P3A17R459727DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R459727DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 935.0 lumens
Efficiency: N/A
Efficacy: 44.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263118

CATALOG NUMBER: P3A17R459727DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1263118

CATALOG NUMBER: P3A17R459727DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198252
5°	194739
10°	184254
15°	168060
20°	148600
25°	129056
30°	110777
35°	92300
40°	68786
45°	42113
50°	19479
55°	15254
60°	14648
65°	13439
70°	12438
75°	11861
80°	10860
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 42113 cd/sqm

TEST NUMBER: P1263118

CATALOG NUMBER: P3A17R459727DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.6	8.8
10°-20°	206.1	22.0
20°-30°	244.9	26.2
30°-40°	212.8	22.8
40°-50°	106.7	11.4
50°-60°	37.0	4.0
60°-70°	26.0	2.8
70°-80°	14.5	1.6
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.6	57.1
0°-40°	746.4	79.8
0°-60°	890.1	95.2
0°-90°	935.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	935.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	904	
5°	885	83
15°	740	206
25°	533	245
35°	345	213
45°	136	107
55°	40	37
65°	26	26
75°	14	15
85°	3	4
90°	0	

TEST NUMBER: P1263118

CATALOG NUMBER: P3A17R459727DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	904.1
2.5°	899.7
5°	884.7
7.5°	861.0
10°	827.5
12.5°	786.6
15°	740.3
17.5°	688.5
20°	636.8
22.5°	584.0
25°	533.4
27.5°	484.9
30°	437.5
32.5°	392.2
35°	344.8
37.5°	294.2
40°	240.3
42.5°	187.5
45°	135.8
47.5°	89.4
50°	57.1
52.5°	44.2
55°	39.9
57.5°	36.6
60°	33.4
62.5°	30.2
65°	25.9
67.5°	22.6
70°	19.4
72.5°	16.2
75°	14.0
77.5°	10.8
80°	8.6
82.5°	6.5
85°	3.2
87.5°	2.2
90°	0.0

(END OF REPORT)