

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263157

Luminaire Tested: P3A17R509727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R509727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 37.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263157

CATALOG NUMBER: P3A17R509727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263157

CATALOG NUMBER: P3A17R509727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231517
5°	225291
10°	207745
15°	182703
20°	152847
25°	121217
30°	88925
35°	61141
40°	38844
45°	21708
50°	11769
55°	9902
60°	8508
65°	7835
70°	6924
75°	6354
80°	5430
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21708 cd/sqm

TEST NUMBER: P1263157

CATALOG NUMBER: P3A17R509727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.8	11.9
10°-20°	222.9	28.0
20°-30°	228.0	28.6
30°-40°	144.6	18.2
40°-50°	57.5	7.2
50°-60°	23.3	2.9
60°-70°	14.9	1.9
70°-80°	7.7	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.7	68.6
0°-40°	690.2	86.7
0°-60°	771.1	96.9
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	1024	95
15°	805	223
25°	501	228
35°	228	145
45°	70	58
55°	26	23
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1263157

CATALOG NUMBER: P3A17R509727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1055.8
2.5°	1048.2
5°	1023.5
7.5°	984.7
10°	933.0
12.5°	871.6
15°	804.8
17.5°	731.5
20°	655.0
22.5°	578.5
25°	501.0
27.5°	423.4
30°	351.2
32.5°	286.6
35°	228.4
37.5°	178.8
40°	135.7
42.5°	100.2
45°	70.0
47.5°	47.4
50°	34.5
52.5°	29.1
55°	25.9
57.5°	22.6
60°	19.4
62.5°	17.2
65°	15.1
67.5°	12.9
70°	10.8
72.5°	8.6
75°	7.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)