

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263880

Luminaire Tested: P3A02R309730DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263880  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R309730DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 123.0 lumens  
Efficiency: N/A  
Efficacy: 34.2 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263880  
CATALOG NUMBER: P3A02R309730DE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1263880  
 CATALOG NUMBER: P3A02R309730DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	58	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39931
5°	37662
10°	32197
15°	25789
20°	20115
25°	15122
30°	11040
35°	7763
40°	5324
45°	3814
50°	3138
55°	3020
60°	3026
65°	3113
70°	3270
75°	3474
80°	3536
85°	4026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 4200 cd/sqm



TEST NUMBER: P1263880  
 CATALOG NUMBER: P3A02R309730DE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	15.5	12.6
10°-20°	31.6	25.7
20°-30°	28.8	23.4
30°-40°	18.3	14.9
40°-50°	9.8	8.0
50°-60°	7.2	5.8
60°-70°	6.0	4.9
70°-80°	4.2	3.4
80°-90°	1.7	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	75.8	61.7
0°-40°	94.1	76.5
0°-60°	111.1	90.3
0°-90°	123.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	123.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	182	
5°	171	15
15°	114	32
25°	62	29
35°	29	18
45°	12	10
55°	8	7
65°	6	6
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P1263880  
CATALOG NUMBER: P3A02R309730DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	182.1
2.5°	179.3
5°	171.1
7.5°	159.1
10°	144.6
12.5°	129.1
15°	113.6
17.5°	99.4
20°	86.2
22.5°	73.9
25°	62.5
27.5°	52.4
30°	43.6
32.5°	35.4
35°	29.0
37.5°	23.0
40°	18.6
42.5°	14.8
45°	12.3
47.5°	10.1
50°	9.2
52.5°	8.5
55°	7.9
57.5°	7.6
60°	6.9
62.5°	6.6
65°	6.0
67.5°	5.7
70°	5.1
72.5°	4.4
75°	4.1
77.5°	3.5
80°	2.8
82.5°	2.5
85°	1.6
87.5°	0.6
90°	0.0

(END OF REPORT)