

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263310

Luminaire Tested: P3A20R159727D010 E3D1LI

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263310  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R159727D010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1830.0 lumens  
Efficiency: N/A  
Efficacy: 63.5 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263310  
CATALOG NUMBER: P3A20R159727D010 E3D1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1263310  
 CATALOG NUMBER: P3A20R159727D010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	99	98	98	98
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	99	98	97	96
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	98	96	95	94
4	107	102	99	96	105	101	98	96	99	97	95	98	96	94	96	94	93	96	94	93	92
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	94	93	91	90
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	93	91	89	88
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	91	89	88	87
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	90	88	86	85
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	89	86	85	89	86	85	84
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	87	85	83	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3484787
5°	2841617
10°	1391646
15°	425950
20°	180382
25°	81585
30°	31802
35°	14670
40°	4580
45°	1737
50°	716
55°	268
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1737 cd/sqm



TEST NUMBER: P1263310  
 CATALOG NUMBER: P3A20R159727D010 E3D1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1004.9	54.9
10°-20°	616.6	33.7
20°-30°	165.6	9.0
30°-40°	36.5	2.0
40°-50°	5.1	0.3
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1787.1	97.7
0°-40°	1823.5	99.6
0°-60°	1829.6	100.0
0°-90°	1830.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1830.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15892	
5°	12910	###
15°	1876	617
25°	337	166
35°	55	36
45°	6	5
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263310  
CATALOG NUMBER: P3A20R159727D010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	15891.9
1°	15792.7
2°	15474.2
3°	14900.3
4°	14036.4
5°	12909.5
6°	11634.8
7°	10215.0
8°	8910.5
9°	7527.5
10°	6250.0
11°	4985.7
12°	3835.9
13°	2950.5
14°	2335.7
15°	1876.3
17.5°	1163.0
20°	773.0
22.5°	520.4
25°	337.2
27.5°	199.8
30°	125.6
32.5°	84.7
35°	54.8
37.5°	30.5
40°	16.0
42.5°	9.0
45°	5.6
47.5°	3.5
50°	2.1
52.5°	1.4
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1263310  
CATALOG NUMBER: P3A20R159727D010 E3D1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)