

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263899

Luminaire Tested: P3A02R359730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R359730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 177.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263899

CATALOG NUMBER: P3A02R359730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263899

CATALOG NUMBER: P3A02R359730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40435
5°	39577
10°	37051
15°	33258
20°	28936
25°	24655
30°	20661
35°	16463
40°	11908
45°	7536
50°	4094
55°	2829
60°	2675
65°	2491
70°	2372
75°	2033
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7536 cd/sqm

TEST NUMBER: P1263899

CATALOG NUMBER: P3A02R359730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.7	9.5
10°-20°	40.8	23.0
20°-30°	46.7	26.4
30°-40°	38.1	21.5
40°-50°	19.2	10.9
50°-60°	7.1	4.0
60°-70°	4.8	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.2	58.9
0°-40°	142.4	80.4
0°-60°	168.7	95.3
0°-90°	177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	177.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	184	
5°	180	17
15°	146	41
25°	102	47
35°	62	38
45°	24	19
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1263899

CATALOG NUMBER: P3A02R359730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	184.4
1°	184.2
2°	183.7
3°	182.9
4°	181.5
5°	179.8
6°	177.6
7°	175.4
8°	172.6
9°	169.7
10°	166.4
11°	163.0
12°	159.2
13°	155.1
14°	150.7
15°	146.5
17.5°	135.4
20°	124.0
22.5°	112.4
25°	101.9
27.5°	91.6
30°	81.6
32.5°	71.5
35°	61.5
37.5°	51.4
40°	41.6
42.5°	32.4
45°	24.3
47.5°	17.5
50°	12.0
52.5°	8.7
55°	7.4
57.5°	6.8
60°	6.1
62.5°	5.5
65°	4.8
67.5°	4.2
70°	3.7
72.5°	3.1
75°	2.4
77.5°	2.0
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4



TEST NUMBER: P1263899

CATALOG NUMBER: P3A02R359730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)