

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263907

Luminaire Tested: P3A02R359730DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R359730DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263907
CATALOG NUMBER: P3A02R359730DE010 E3PHLD1MW

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - · - · - 90°-270°



TEST NUMBER: P1263907
 CATALOG NUMBER: P3A02R359730DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	77	73	70	68
4	88	78	71	65	86	77	70	65	75	68	64	72	67	63	70	66	62	70	66	62	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	65	60	56	54
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	55	50	46	55	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	52	46	42	41
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	48	43	39	38
10	60	49	42	37	59	48	41	37	47	41	37	46	41	36	45	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27739	27739	27739
5°	27229	27163	27229
10°	25584	25539	25584
15°	23178	23178	23224
20°	20512	20512	20512
25°	17832	17783	17783
30°	15471	15344	15420
35°	13304	13251	13304
40°	11565	11479	11565
45°	10141	10079	10079
50°	9006	8938	8938
55°	7914	7914	7914
60°	7192	7061	7192
65°	6434	6434	6434
70°	5706	5706	5706
75°	5168	4999	5168
80°	4420	4420	4420
85°	2768	2768	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10141 cd/sqm



TEST NUMBER: P1263907
 CATALOG NUMBER: P3A02R359730DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.5	6.8
10°-20°	28.5	16.8
20°-30°	33.8	20.0
30°-40°	31.1	18.4
40°-50°	25.2	14.9
50°-60°	18.7	11.0
60°-70°	12.3	7.3
70°-80°	6.4	3.8
80°-90°	1.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	73.8	43.7
0°-40°	104.9	62.1
0°-60°	148.8	88.1
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	126	126	126	126	126	
5°	124	123	123	123	124	12
15°	102	102	102	102	102	28
25°	74	74	74	74	74	34
35°	50	50	50	50	50	31
45°	33	32	32	32	32	25
55°	21	21	21	21	21	19
65°	12	12	12	12	12	12
75°	6	6	6	6	6	6
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P1263907

CATALOG NUMBER: P3A02R359730DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	126.5	126.5	126.5	126.5	126.5
1°	126.5	126.3	126.3	126.3	126.5
2°	126.1	126.1	126.1	126.1	126.1
3°	125.6	125.4	125.4	125.4	125.4
4°	124.8	124.5	124.5	124.5	124.5
5°	123.7	123.4	123.4	123.4	123.7
6°	122.4	122.1	121.9	121.9	122.1
7°	121.1	120.6	120.6	120.6	120.6
8°	119.1	118.9	118.9	118.9	118.9
9°	117.1	116.7	116.9	116.9	116.9
10°	114.9	114.7	114.7	114.7	114.9
11°	112.8	112.5	112.5	112.3	112.5
12°	110.1	110.1	110.1	110.1	110.1
13°	107.7	107.5	107.5	107.5	107.7
14°	105.1	104.9	104.9	104.9	104.9
15°	102.1	102.1	102.1	102.1	102.3
17.5°	95.1	94.9	95.1	95.1	95.3
20°	87.9	87.7	87.9	87.9	87.9
22.5°	80.7	80.7	80.5	80.7	80.9
25°	73.7	73.5	73.5	73.7	73.5
27.5°	67.2	67.0	67.0	67.0	67.0
30°	61.1	60.6	60.6	60.9	60.9
32.5°	54.7	54.7	55.0	54.7	54.7
35°	49.7	49.5	49.5	49.7	49.7
37.5°	44.7	44.5	44.5	44.7	44.7
40°	40.4	40.4	40.1	40.4	40.4
42.5°	36.2	36.2	36.2	36.2	36.2
45°	32.7	32.5	32.5	32.5	32.5
47.5°	29.2	29.2	29.2	29.0	29.2
50°	26.4	26.2	26.2	26.2	26.2
52.5°	23.3	23.3	23.3	23.3	23.3
55°	20.7	20.7	20.7	20.7	20.7
57.5°	18.5	18.3	18.3	18.3	18.3
60°	16.4	16.4	16.1	16.4	16.4
62.5°	14.2	14.2	14.2	14.2	14.2
65°	12.4	12.4	12.4	12.4	12.4
67.5°	10.7	10.7	10.7	10.7	10.7
70°	8.9	8.9	8.9	8.9	8.9
72.5°	7.6	7.4	7.4	7.4	7.4
75°	6.1	6.1	5.9	6.1	6.1
77.5°	4.6	4.6	4.6	4.6	4.6
80°	3.5	3.5	3.5	3.3	3.5
82.5°	2.2	2.2	2.2	2.2	2.2
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.2	0.2	0.2	0.4	0.4



TEST NUMBER: P1263907
CATALOG NUMBER: P3A02R359730DE010 E3PHLD1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)