

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263951

Luminaire Tested: P3A02R459730DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263951  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R459730DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 93.0 lumens  
Efficiency: N/A  
Efficacy: 25.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263951  
CATALOG NUMBER: P3A02R459730DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1263951

CATALOG NUMBER: P3A02R459730DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	19713
5°	19370
10°	18325
15°	16708
20°	14771
25°	12848
30°	11014
35°	9182
40°	6841
45°	4186
50°	1944
55°	1529
60°	1447
65°	1349
70°	1218
75°	1186
80°	1137
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4186 cd/sqm



TEST NUMBER: P1263951  
 CATALOG NUMBER: P3A02R459730DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	8.2	8.8
10°-20°	20.5	22.0
20°-30°	24.4	26.2
30°-40°	21.2	22.8
40°-50°	10.6	11.4
50°-60°	3.7	4.0
60°-70°	2.6	2.8
70°-80°	1.5	1.6
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	53.1	57.1
0°-40°	74.2	79.8
0°-60°	88.5	95.2
0°-90°	93.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	93.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	90	
5°	88	8
15°	74	20
25°	53	24
35°	34	21
45°	14	11
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1263951  
CATALOG NUMBER: P3A02R459730DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	89.9
2.5°	89.5
5°	88.0
7.5°	85.6
10°	82.3
12.5°	78.2
15°	73.6
17.5°	68.5
20°	63.3
22.5°	58.1
25°	53.1
27.5°	48.2
30°	43.5
32.5°	39.0
35°	34.3
37.5°	29.3
40°	23.9
42.5°	18.6
45°	13.5
47.5°	8.9
50°	5.7
52.5°	4.4
55°	4.0
57.5°	3.6
60°	3.3
62.5°	3.0
65°	2.6
67.5°	2.3
70°	1.9
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)