

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263986

Luminaire Tested: P3A02R509730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R509730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 78.9 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263986

CATALOG NUMBER: P3A02R509730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263986

CATALOG NUMBER: P3A02R509730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	62		69
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	62	56	52	70	61	55	52	60	55	52		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22981
5°	22364
10°	20619
15°	18139
20°	15168
25°	12025
30°	8837
35°	6077
40°	3864
45°	2140
50°	1160
55°	994
60°	833
65°	778
70°	705
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2140 cd/sqm

TEST NUMBER: P1263986

CATALOG NUMBER: P3A02R509730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.4	11.9
10°-20°	22.1	28.0
20°-30°	22.6	28.7
30°-40°	14.3	18.2
40°-50°	5.7	7.2
50°-60°	2.3	2.9
60°-70°	1.5	1.9
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	54.2	68.6
0°-40°	68.5	86.8
0°-60°	76.5	96.9
0°-90°	78.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	78.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	105	
5°	102	9
15°	80	22
25°	50	23
35°	23	14
45°	7	6
55°	3	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1263986

CATALOG NUMBER: P3A02R509730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	104.8
2.5°	104.0
5°	101.6
7.5°	97.7
10°	92.6
12.5°	86.5
15°	79.9
17.5°	72.6
20°	65.0
22.5°	57.4
25°	49.7
27.5°	42.0
30°	34.9
32.5°	28.4
35°	22.7
37.5°	17.7
40°	13.5
42.5°	9.9
45°	6.9
47.5°	4.7
50°	3.4
52.5°	2.9
55°	2.6
57.5°	2.2
60°	1.9
62.5°	1.7
65°	1.5
67.5°	1.3
70°	1.1
72.5°	0.9
75°	0.7
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)