

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263992

Luminaire Tested: P3A02R559730DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R559730DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 291.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263992

CATALOG NUMBER: P3A02R559730DE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1263992

CATALOG NUMBER: P3A02R559730DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		112	109	107	105		105	104	102		101	100	99		98	97	96
2	109	104	101	98		107	103	99	96		100	97	94		97	94	92		94	92	90
3	104	98	94	90		102	97	93	89		94	91	88		92	89	86		90	87	85
4	99	92	87	84		98	91	87	83		89	85	82		87	84	81		86	83	80
5	95	87	82	78		93	86	81	78		85	80	77		83	79	76		82	78	76
6	91	83	77	73		89	82	77	73		80	76	72		79	75	72		78	74	72
7	87	78	73	69		85	78	72	69		76	72	68		75	71	68		74	70	68
8	83	74	69	65		82	74	69	65		73	68	65		72	67	64		71	67	64
9	79	71	65	61		78	70	65	61		69	64	61		68	64	61		68	64	61
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80717
5°	79969
10°	83165
15°	82021
20°	75630
25°	61528
30°	37373
35°	12930
40°	3693
45°	1768
50°	751
55°	344
60°	395
65°	363
70°	256
75°	339
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1768 cd/sqm

TEST NUMBER: P1263992

CATALOG NUMBER: P3A02R559730DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.1	12.1
10°-20°	100.4	34.5
20°-30°	111.9	38.5
30°-40°	36.6	12.6
40°-50°	4.8	1.7
50°-60°	1.0	0.4
60°-70°	0.6	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	247.5	85.1
0°-40°	284.1	97.6
0°-60°	289.9	99.6
0°-90°	291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	368	
5°	363	35
15°	361	100
25°	254	112
35°	48	37
45°	6	5
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1263992

CATALOG NUMBER: P3A02R559730DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	368.1
2.5°	365.4
5°	363.3
7.5°	368.5
10°	373.5
12.5°	370.9
15°	361.3
17.5°	346.0
20°	324.1
22.5°	293.9
25°	254.3
27.5°	204.0
30°	147.6
32.5°	90.5
35°	48.3
37.5°	24.5
40°	12.9
42.5°	8.3
45°	5.7
47.5°	3.9
50°	2.2
52.5°	1.3
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.7
65°	0.7
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)