

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263547

Luminaire Tested: P3A20R559727D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R559727D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 756.0 lumens
Efficiency: N/A
Efficacy: 26.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263547

CATALOG NUMBER: P3A20R559727D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263547

CATALOG NUMBER: P3A20R559727D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207593
5°	205480
10°	198438
15°	183429
20°	158284
25°	125015
30°	88672
35°	57179
40°	34350
45°	19351
50°	10405
55°	3708
60°	3333
65°	3217
70°	3142
75°	2965
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19351 cd/sqm

TEST NUMBER: P1263547

CATALOG NUMBER: P3A20R559727D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.8	11.6
10°-20°	223.4	29.6
20°-30°	234.1	31.0
30°-40°	136.6	18.1
40°-50°	51.1	6.8
50°-60°	12.0	1.6
60°-70°	6.1	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.4	72.1
0°-40°	682.0	90.2
0°-60°	745.1	98.6
0°-90°	756.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	756.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	947	
5°	934	88
15°	808	223
25°	517	234
35°	214	137
45°	62	51
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1263547

CATALOG NUMBER: P3A20R559727D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	946.7
2.5°	943.9
5°	933.5
7.5°	916.9
10°	891.2
12.5°	855.1
15°	808.0
17.5°	748.3
20°	678.3
22.5°	599.9
25°	516.7
27.5°	431.4
30°	350.2
32.5°	276.7
35°	213.6
37.5°	162.3
40°	120.0
42.5°	86.0
45°	62.4
47.5°	45.1
50°	30.5
52.5°	17.3
55°	9.7
57.5°	8.3
60°	7.6
62.5°	6.9
65°	6.2
67.5°	5.5
70°	4.9
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)