

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263999

Luminaire Tested: P3A02R559730DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R559730DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 282.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263999

CATALOG NUMBER: P3A02R559730DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1263999

CATALOG NUMBER: P3A02R559730DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	83	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81770
5°	78890
10°	81695
15°	80545
20°	74556
25°	60294
30°	36132
35°	12234
40°	3378
45°	1489
50°	443
55°	76
60°	44
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1489 cd/sqm

TEST NUMBER: P1263999

CATALOG NUMBER: P3A02R559730DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.7	12.3
10°-20°	98.8	35.0
20°-30°	109.8	38.9
30°-40°	34.2	12.1
40°-50°	4.1	1.5
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	243.3	86.3
0°-40°	277.5	98.4
0°-60°	281.9	100.0
0°-90°	282.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	282.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	373	
5°	358	35
15°	355	99
25°	249	110
35°	46	34
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1263999

CATALOG NUMBER: P3A02R559730DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	372.9
1°	371.5
2°	367.9
3°	363.4
4°	359.3
5°	358.4
6°	359.4
7°	361.7
8°	364.3
9°	366.3
10°	366.9
11°	366.5
12°	364.8
13°	362.1
14°	359.0
15°	354.8
16°	350.0
17°	343.9
18°	337.0
19°	328.8
20°	319.5
21°	308.9
22°	296.3
23°	282.5
24°	266.7
25°	249.2
26°	230.0
27°	209.7
28°	187.9
29°	165.5
30°	142.7
31°	119.8
32°	97.4
32.5°	87.4
33°	77.1
34°	59.7
35°	45.7
36°	34.8
37°	25.8
37.5°	22.1
38°	19.2
39°	14.6
40°	11.8
42.5°	7.5
45°	4.8



TEST NUMBER: P1263999
CATALOG NUMBER: P3A02R559730DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.9
50°	1.3
52.5°	0.4
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)