

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263622

Luminaire Tested: P3A20R659727D010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263622  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R659727D010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 981.0 lumens  
Efficiency: N/A  
Efficacy: 34.1 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263622  
CATALOG NUMBER: P3A20R659727D010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1263622  
 CATALOG NUMBER: P3A20R659727D010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	249344
5°	243143
10°	226426
15°	202930
20°	175249
25°	145775
30°	114954
35°	85180
40°	58710
45°	36407
50°	19786
55°	12425
60°	10525
65°	9547
70°	8142
75°	7202
80°	7198
85°	7045

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 36407 cd/sqm



TEST NUMBER: P1263622  
 CATALOG NUMBER: P3A20R659727D010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.6	10.5
10°-20°	248.4	25.3
20°-30°	274.7	28.0
30°-40°	199.5	20.3
40°-50°	93.5	9.5
50°-60°	31.5	3.2
60°-70°	18.2	1.9
70°-80°	9.5	1.0
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.8	63.8
0°-40°	825.3	84.1
0°-60°	950.2	96.9
0°-90°	981.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	981.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1137	
5°	1105	103
15°	894	248
25°	602	275
35°	318	200
45°	117	93
55°	32	31
65°	18	18
75°	8	10
85°	3	3
90°	0	



TEST NUMBER: P1263622

CATALOG NUMBER: P3A20R659727D010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1137.1
2.5°	1130.1
5°	1104.6
7.5°	1066.4
10°	1016.9
12.5°	958.9
15°	893.9
17.5°	823.2
20°	751.0
22.5°	676.1
25°	602.5
27.5°	527.6
30°	454.0
32.5°	383.3
35°	318.2
37.5°	258.8
40°	205.1
42.5°	157.0
45°	117.4
47.5°	84.9
50°	58.0
52.5°	39.6
55°	32.5
57.5°	28.3
60°	24.0
62.5°	21.2
65°	18.4
67.5°	15.6
70°	12.7
72.5°	11.3
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)