

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264061

Luminaire Tested: P3A02R659730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R659730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 107.0 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264061

CATALOG NUMBER: P3A02R659730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264061

CATALOG NUMBER: P3A02R659730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		58
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25239
5°	24939
10°	23981
15°	22475
20°	20208
25°	17154
30°	13420
35°	9557
40°	6269
45°	3876
50°	1979
55°	688
60°	614
65°	623
70°	577
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3876 cd/sqm

TEST NUMBER: P1264061

CATALOG NUMBER: P3A02R659730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.6	9.9
10°-20°	27.5	25.7
20°-30°	32.2	30.1
30°-40°	22.5	21.0
40°-50°	9.9	9.3
50°-60°	2.2	2.1
60°-70°	1.2	1.1
70°-80°	0.6	0.6
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	70.4	65.8
0°-40°	92.9	86.8
0°-60°	105.0	98.1
0°-90°	107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	107.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	115	
5°	113	11
15°	99	28
25°	71	32
35°	36	23
45°	12	10
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264061

CATALOG NUMBER: P3A02R659730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	115.1
2.5°	114.6
5°	113.3
7.5°	110.9
10°	107.7
12.5°	103.8
15°	99.0
17.5°	93.1
20°	86.6
22.5°	79.2
25°	70.9
27.5°	62.2
30°	53.0
32.5°	44.2
35°	35.7
37.5°	28.4
40°	21.9
42.5°	16.5
45°	12.5
47.5°	9.2
50°	5.8
52.5°	3.0
55°	1.8
57.5°	1.6
60°	1.4
62.5°	1.3
65°	1.2
67.5°	1.0
70°	0.9
72.5°	0.7
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)