

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264162

Luminaire Tested: P3A05R129730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264162
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R129730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 342.0 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264162
CATALOG NUMBER: P3A05R129730DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1264162
 CATALOG NUMBER: P3A05R129730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65				65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60				60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56				56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52				52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49				49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86265
5°	83931
10°	76685
15°	67174
20°	57638
25°	48124
30°	38512
35°	28884
40°	20954
45°	13707
50°	8563
55°	5811
60°	5131
65°	4722
70°	4424
75°	4067
80°	3788
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13707 cd/sqm



TEST NUMBER: P1264162
 CATALOG NUMBER: P3A05R129730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	10.3
10°-20°	82.4	24.1
20°-30°	90.9	26.6
30°-40°	68.0	19.9
40°-50°	35.3	10.3
50°-60°	14.6	4.3
60°-70°	9.1	2.6
70°-80°	5.1	1.5
80°-90°	1.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.5	61.0
0°-40°	276.5	80.9
0°-60°	326.4	95.4
0°-90°	342.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	342.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	393	
5°	381	35
15°	296	82
25°	199	91
35°	108	68
45°	44	35
55°	15	15
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1264162
CATALOG NUMBER: P3A05R129730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	393.4
1°	393.8
2°	392.5
3°	389.9
4°	386.0
5°	381.3
6°	375.2
7°	368.7
8°	360.9
9°	352.7
10°	344.4
12.5°	320.6
15°	295.9
17.5°	271.2
20°	247.0
22.5°	222.3
25°	198.9
27.5°	175.5
30°	152.1
32.5°	129.1
35°	107.9
37.5°	89.7
40°	73.2
42.5°	58.1
45°	44.2
47.5°	33.4
50°	25.1
52.5°	18.6
55°	15.2
57.5°	13.4
60°	11.7
62.5°	10.4
65°	9.1
67.5°	7.8
70°	6.9
72.5°	5.6
75°	4.8
77.5°	3.9
80°	3.0
82.5°	2.2
85°	1.3
87.5°	0.4
90°	0.0

(END OF REPORT)