

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264196

Luminaire Tested: P3A05R159730DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R159730DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 275.9 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264196

CATALOG NUMBER: P3A05R159730DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1264196

CATALOG NUMBER: P3A05R159730DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	97	93
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	91	89
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	84	82
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	78	75
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	73	70
5	93	84	78	74	91	83	78	74	81	77	73	80	76	73	78	75	72	70	68	66
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	64	62
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	60	59
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	57	56
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	54	53
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119026
5°	109993
10°	87818
15°	66334
20°	50521
25°	38494
30°	27574
35°	17989
40°	11021
45°	6667
50°	4435
55°	3441
60°	2938
65°	2542
70°	2308
75°	2288
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6667 cd/sqm

TEST NUMBER: P1264196

CATALOG NUMBER: P3A05R159730DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	16.0
10°-20°	81.7	29.6
20°-30°	72.7	26.4
30°-40°	43.0	15.6
40°-50°	17.7	6.4
50°-60°	8.3	3.0
60°-70°	5.0	1.8
70°-80°	2.6	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	198.7	72.0
0°-40°	241.7	87.6
0°-60°	267.6	97.0
0°-90°	275.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	543	
5°	500	44
15°	292	82
25°	159	73
35°	67	43
45°	22	18
55°	9	8
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1264196

CATALOG NUMBER: P3A05R159730DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	542.8
1°	541.4
2°	537.4
3°	529.3
4°	515.9
5°	499.7
6°	482.3
7°	461.6
8°	440.1
9°	418.2
10°	394.4
12.5°	340.2
15°	292.2
17.5°	251.0
20°	216.5
22.5°	186.0
25°	159.1
27.5°	133.1
30°	108.9
32.5°	86.9
35°	67.2
37.5°	51.5
40°	38.5
42.5°	28.7
45°	21.5
47.5°	16.6
50°	13.0
52.5°	10.8
55°	9.0
57.5°	7.6
60°	6.7
62.5°	5.8
65°	4.9
67.5°	4.5
70°	3.6
72.5°	3.1
75°	2.7
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)