

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264254

Luminaire Tested: P3A05R259730DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264254  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R259730DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 287.9 lumens  
Efficiency: N/A  
Efficacy: 40.0 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264254  
CATALOG NUMBER: P3A05R259730DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264254

CATALOG NUMBER: P3A05R259730DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	104553
5°	100308
10°	87885
15°	70647
20°	54278
25°	41059
30°	29675
35°	19702
40°	11965
45°	6946
50°	4435
55°	3594
60°	3158
65°	2802
70°	2308
75°	2288
80°	1642
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6946 cd/sqm



TEST NUMBER: P1264254  
 CATALOG NUMBER: P3A05R259730DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.5	14.4
10°-20°	86.0	29.9
20°-30°	77.8	27.0
30°-40°	46.7	16.2
40°-50°	18.6	6.4
50°-60°	8.6	3.0
60°-70°	5.2	1.8
70°-80°	2.8	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.3	71.3
0°-40°	252.1	87.5
0°-60°	279.2	97.0
0°-90°	287.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	287.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	477	
5°	456	41
15°	311	86
25°	170	78
35°	74	47
45°	22	19
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1264254  
CATALOG NUMBER: P3A05R259730DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	476.8
1°	476.8
2°	474.6
3°	469.6
4°	463.4
5°	455.7
6°	445.9
7°	434.6
8°	421.6
9°	408.6
10°	394.7
11°	378.5
12°	361.9
13°	345.3
14°	328.7
15°	311.2
17.5°	269.8
20°	232.6
22.5°	198.9
25°	169.7
27.5°	142.3
30°	117.2
32.5°	94.3
35°	73.6
37.5°	56.1
40°	41.8
42.5°	30.5
45°	22.4
47.5°	17.1
50°	13.0
52.5°	10.8
55°	9.4
57.5°	8.1
60°	7.2
62.5°	5.8
65°	5.4
67.5°	4.5
70°	3.6
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.3
82.5°	0.9
85°	0.9
87.5°	0.4



TEST NUMBER: P1264254  
CATALOG NUMBER: P3A05R259730DE010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)