

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426179

Luminaire Tested: P3A05RH9727DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426179
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05RH9727DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 2700K CCT AND, 97CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 201.0 lumens
Efficiency: N/A
Efficacy: 27.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426179

CATALOG NUMBER: P3A05RH9727DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426179

CATALOG NUMBER: P3A05RH9727DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96922
5°	88796
10°	77598
15°	68082
20°	34443
25°	17154
30°	15496
35°	11778
40°	8273
45°	5582
50°	3582
55°	2409
60°	1667
65°	1297
70°	833
75°	678
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5582 cd/sqm

TEST NUMBER: P1426179

CATALOG NUMBER: P3A05RH9727DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	18.3
10°-20°	76.0	37.8
20°-30°	37.0	18.4
30°-40°	27.7	13.8
40°-50°	14.2	7.1
50°-60°	5.9	2.9
60°-70°	2.4	1.2
70°-80°	0.9	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.8	74.5
0°-40°	177.4	88.3
0°-60°	197.6	98.3
0°-90°	201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	442	
5°	403	37
15°	300	76
25°	71	37
35°	44	28
45°	18	14
55°	6	6
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1426179

CATALOG NUMBER: P3A05RH9727DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	442.0
2.5°	432.0
5°	403.4
7.5°	372.8
10°	348.5
12.5°	330.5
15°	299.9
17.5°	234.0
20°	147.6
22.5°	87.6
25°	70.9
27.5°	65.4
30°	61.2
32.5°	53.7
35°	44.0
37.5°	36.1
40°	28.9
42.5°	23.1
45°	18.0
47.5°	13.8
50°	10.5
52.5°	8.0
55°	6.3
57.5°	5.0
60°	3.8
62.5°	2.9
65°	2.5
67.5°	1.7
70°	1.3
72.5°	1.3
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)