

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264951

Luminaire Tested: P3A13R129730DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264951  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R129730DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 621.0 lumens  
Efficiency: N/A  
Efficacy: 40.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264951  
CATALOG NUMBER: P3A13R129730DE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1264951  
 CATALOG NUMBER: P3A13R129730DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156632
5°	152388
10°	139254
15°	121976
20°	104636
25°	87368
30°	69909
35°	52441
40°	38071
45°	24871
50°	15556
55°	10513
60°	9298
65°	8561
70°	8078
75°	7371
80°	6945
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24871 cd/sqm



TEST NUMBER: P1264951  
 CATALOG NUMBER: P3A13R129730DE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.9	10.3
10°-20°	149.7	24.1
20°-30°	165.0	26.6
30°-40°	123.5	19.9
40°-50°	64.0	10.3
50°-60°	26.5	4.3
60°-70°	16.4	2.6
70°-80°	9.2	1.5
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.6	61.0
0°-40°	502.1	80.9
0°-60°	592.6	95.4
0°-90°	621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	714	
5°	692	64
15°	537	150
25°	361	165
35°	196	124
45°	80	64
55°	28	27
65°	16	16
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1264951  
CATALOG NUMBER: P3A13R129730DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	714.3
1°	715.1
2°	712.8
3°	708.0
4°	701.0
5°	692.3
6°	681.3
7°	669.5
8°	655.3
9°	640.4
10°	625.4
12.5°	582.2
15°	537.3
17.5°	492.5
20°	448.4
22.5°	403.6
25°	361.1
27.5°	318.6
30°	276.1
32.5°	234.4
35°	195.9
37.5°	162.8
40°	133.0
42.5°	105.4
45°	80.2
47.5°	60.6
50°	45.6
52.5°	33.8
55°	27.5
57.5°	24.4
60°	21.2
62.5°	18.9
65°	16.5
67.5°	14.2
70°	12.6
72.5°	10.2
75°	8.7
77.5°	7.1
80°	5.5
82.5°	3.9
85°	2.4
87.5°	0.8
90°	0.0

(END OF REPORT)