

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264370

Luminaire Tested: P3A05R459730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R459730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 323.9 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264370
CATALOG NUMBER: P3A05R459730DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264370
 CATALOG NUMBER: P3A05R459730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96505
5°	94299
10°	86995
15°	75642
20°	62142
25°	48342
30°	35702
35°	25136
40°	15687
45°	8497
50°	4605
55°	3938
60°	3552
65°	3009
70°	2565
75°	2626
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8497 cd/sqm



TEST NUMBER: P1264370
 CATALOG NUMBER: P3A05R459730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	12.2
10°-20°	92.1	28.4
20°-30°	91.4	28.2
30°-40°	58.9	18.2
40°-50°	22.7	7.0
50°-60°	9.2	2.8
60°-70°	5.8	1.8
70°-80°	3.1	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.2	68.9
0°-40°	282.2	87.1
0°-60°	314.1	97.0
0°-90°	323.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	323.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	440	
5°	428	40
15°	333	92
25°	200	91
35°	94	59
45°	27	23
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1264370
CATALOG NUMBER: P3A05R459730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	440.1
2.5°	437.9
5°	428.4
7.5°	412.3
10°	390.7
12.5°	363.8
15°	333.2
17.5°	300.0
20°	266.3
22.5°	232.2
25°	199.8
27.5°	169.3
30°	141.0
32.5°	116.3
35°	93.9
37.5°	73.7
40°	54.8
42.5°	39.5
45°	27.4
47.5°	18.4
50°	13.5
52.5°	11.2
55°	10.3
57.5°	9.0
60°	8.1
62.5°	6.7
65°	5.8
67.5°	4.9
70°	4.0
72.5°	3.6
75°	3.1
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)