

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264960

Luminaire Tested: P3A13R159730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R159730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1102.0 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264960
CATALOG NUMBER: P3A13R159730DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1264960
 CATALOG NUMBER: P3A13R159730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	98	97	95	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	97	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	95	93	92	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	94	92	90	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	92	90	89	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	91	89	87	86
9	97	92	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	90	87	86	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	88	86	85	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2142021
5°	1795219
10°	845631
15°	254939
20°	94345
25°	36680
30°	13673
35°	4203
40°	1489
45°	806
50°	580
55°	650
60°	746
65°	467
70°	577
75°	763
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 806 cd/sqm



TEST NUMBER: P1264960
 CATALOG NUMBER: P3A13R159730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.5	57.2
10°-20°	374.8	34.0
20°-30°	78.7	7.1
30°-40°	12.7	1.2
40°-50°	2.1	0.2
50°-60°	1.5	0.1
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1084.0	98.4
0°-40°	1096.7	99.5
0°-60°	1100.4	99.9
0°-90°	1102.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9768	
5°	8156	631
15°	1123	375
25°	152	79
35°	16	13
45°	3	2
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1264960
CATALOG NUMBER: P3A13R159730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	9768.4
1°	9737.9
2°	9582.8
3°	9272.7
4°	8817.9
5°	8155.7
6°	7377.7
7°	6488.2
8°	5638.7
9°	4676.9
10°	3797.8
12.5°	2049.2
15°	1123.0
17.5°	657.8
20°	404.3
22.5°	247.4
25°	151.6
27.5°	91.5
30°	54.0
32.5°	30.5
35°	15.7
37.5°	8.7
40°	5.2
42.5°	3.5
45°	2.6
47.5°	1.7
50°	1.7
52.5°	1.7
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)