

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264469

Luminaire Tested: P3A05R659730DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R659730DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 554.9 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264469

CATALOG NUMBER: P3A05R659730DE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1264469

CATALOG NUMBER: P3A05R659730DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135625
5°	127647
10°	126028
15°	123815
20°	116887
25°	108490
30°	84317
35°	48774
40°	19665
45°	9055
50°	3514
55°	1376
60°	1184
65°	1141
70°	1154
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9055 cd/sqm

TEST NUMBER: P1264469

CATALOG NUMBER: P3A05R659730DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.1	9.9
10°-20°	152.3	27.4
20°-30°	199.4	35.9
30°-40°	115.5	20.8
40°-50°	24.7	4.5
50°-60°	4.0	0.7
60°-70°	2.2	0.4
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.8	73.3
0°-40°	522.3	94.1
0°-60°	551.0	99.3
0°-90°	554.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	554.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	618	
5°	580	55
15°	545	152
25°	448	199
35°	182	115
45°	29	25
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264469

CATALOG NUMBER: P3A05R659730DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	618.5
2.5°	601.0
5°	579.9
7.5°	571.4
10°	566.0
12.5°	558.4
15°	545.4
17.5°	525.2
20°	500.9
22.5°	478.0
25°	448.4
27.5°	398.6
30°	333.0
32.5°	258.1
35°	182.2
37.5°	115.4
40°	68.7
42.5°	43.1
45°	29.2
47.5°	18.9
50°	10.3
52.5°	4.9
55°	3.6
57.5°	3.1
60°	2.7
62.5°	2.7
65°	2.2
67.5°	1.8
70°	1.8
72.5°	1.3
75°	1.3
77.5°	0.9
80°	0.9
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)