

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265011

Luminaire Tested: P3A13R209730DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R209730DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 686.0 lumens
Efficiency: N/A
Efficacy: 47.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265011

CATALOG NUMBER: P3A13R209730DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1265011

CATALOG NUMBER: P3A13R209730DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169679
5°	165155
10°	151923
15°	133735
20°	114693
25°	96344
30°	77885
35°	59240
40°	42165
45°	27848
50°	17228
55°	11316
60°	10306
65°	9495
70°	8912
75°	8133
80°	7703
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 27848 cd/sqm

TEST NUMBER: P1265011

CATALOG NUMBER: P3A13R209730DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	10.1
10°-20°	164.0	23.9
20°-30°	182.0	26.5
30°-40°	138.9	20.2
40°-50°	71.1	10.4
50°-60°	29.2	4.3
60°-70°	18.2	2.7
70°-80°	10.2	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.4	60.6
0°-40°	554.3	80.8
0°-60°	654.6	95.4
0°-90°	686.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	750	69
15°	589	164
25°	398	182
35°	221	139
45°	90	71
55°	30	29
65°	18	18
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P1265011

CATALOG NUMBER: P3A13R209730DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	773.8
1°	774.7
2°	771.2
3°	766.8
4°	759.9
5°	750.3
6°	739.0
7°	726.8
8°	713.7
9°	698.0
10°	682.3
12.5°	637.0
15°	589.1
17.5°	540.3
20°	491.5
22.5°	442.7
25°	398.2
27.5°	353.8
30°	307.6
32.5°	264.0
35°	221.3
37.5°	183.9
40°	147.3
42.5°	115.9
45°	89.8
47.5°	68.0
50°	50.5
52.5°	37.5
55°	29.6
57.5°	27.0
60°	23.5
62.5°	20.9
65°	18.3
67.5°	15.7
70°	13.9
72.5°	11.3
75°	9.6
77.5°	7.8
80°	6.1
82.5°	4.4
85°	2.6
87.5°	0.9
90°	0.0

(END OF REPORT)