

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426185

Luminaire Tested: P3A05RH9730DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05RH9730DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 3000K CCT AND, 97CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 214.9 lumens
Efficiency: N/A
Efficacy: 29.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426185

CATALOG NUMBER: P3A05RH9730DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426185

CATALOG NUMBER: P3A05RH9730DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	92	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103676
5°	94981
10°	83009
15°	72804
20°	36847
25°	18340
30°	16585
35°	12608
40°	8874
45°	5985
50°	3821
55°	2561
60°	1754
65°	1401
70°	833
75°	763
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5985 cd/sqm

TEST NUMBER: P1426185

CATALOG NUMBER: P3A05RH9730DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	18.3
10°-20°	81.3	37.8
20°-30°	39.6	18.4
30°-40°	29.6	13.8
40°-50°	15.3	7.1
50°-60°	6.3	2.9
60°-70°	2.5	1.2
70°-80°	0.9	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.2	74.5
0°-40°	189.8	88.3
0°-60°	211.3	98.3
0°-90°	214.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	214.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	473	
5°	432	39
15°	321	81
25°	76	40
35°	47	30
45°	19	15
55°	7	6
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1426185

CATALOG NUMBER: P3A05RH9730DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	472.8
2.5°	462.0
5°	431.5
7.5°	398.8
10°	372.8
12.5°	353.5
15°	320.7
17.5°	250.3
20°	157.9
22.5°	93.8
25°	75.8
27.5°	70.0
30°	65.5
32.5°	57.4
35°	47.1
37.5°	38.6
40°	31.0
42.5°	24.7
45°	19.3
47.5°	14.8
50°	11.2
52.5°	8.5
55°	6.7
57.5°	5.4
60°	4.0
62.5°	3.1
65°	2.7
67.5°	1.8
70°	1.3
72.5°	1.3
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)