

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265040

Luminaire Tested: P3A13R259730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R259730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 274.0 lumens
Efficiency: N/A
Efficacy: 18.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265040

CATALOG NUMBER: P3A13R259730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265040

CATALOG NUMBER: P3A13R259730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99488
5°	95443
10°	83610
15°	67197
20°	51641
25°	39075
30°	28232
35°	18765
40°	11364
45°	6636
50°	4230
55°	3441
60°	2982
65°	2646
70°	2180
75°	2203
80°	1642
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6636 cd/sqm

TEST NUMBER: P1265040

CATALOG NUMBER: P3A13R259730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	14.4
10°-20°	81.9	29.9
20°-30°	74.0	27.0
30°-40°	44.5	16.2
40°-50°	17.7	6.4
50°-60°	8.2	3.0
60°-70°	5.0	1.8
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	195.4	71.3
0°-40°	239.8	87.5
0°-60°	265.6	96.9
0°-90°	274.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	274.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	454	
5°	434	39
15°	296	82
25°	162	74
35°	70	44
45°	21	18
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265040

CATALOG NUMBER: P3A13R259730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	453.7
1°	453.7
2°	451.5
3°	446.8
4°	440.8
5°	433.6
6°	424.2
7°	413.5
8°	401.1
9°	388.7
10°	375.5
11°	360.1
12°	344.3
13°	328.5
14°	312.7
15°	296.0
17.5°	256.7
20°	221.3
22.5°	189.2
25°	161.5
27.5°	135.4
30°	111.5
32.5°	89.7
35°	70.1
37.5°	53.4
40°	39.7
42.5°	29.0
45°	21.4
47.5°	16.2
50°	12.4
52.5°	10.3
55°	9.0
57.5°	7.7
60°	6.8
62.5°	5.6
65°	5.1
67.5°	4.3
70°	3.4
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.3
82.5°	0.9
85°	0.9
87.5°	0.4



TEST NUMBER: P1265040

CATALOG NUMBER: P3A13R259730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)