

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264633

Luminaire Tested: P3A09R259730DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R259730DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 687.1 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264633

CATALOG NUMBER: P3A09R259730DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1264633

CATALOG NUMBER: P3A09R259730DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440688
5°	411159
10°	329364
15°	223565
20°	135275
25°	79117
30°	45045
35°	24788
40°	13168
45°	6915
50°	4025
55°	3020
60°	2588
65°	2750
70°	2500
75°	2203
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6915 cd/sqm

TEST NUMBER: P1264633

CATALOG NUMBER: P3A09R259730DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.8	24.1
10°-20°	270.8	39.4
20°-30°	154.7	22.5
30°-40°	61.1	8.9
40°-50°	18.7	2.7
50°-60°	7.4	1.1
60°-70°	5.0	0.7
70°-80°	2.8	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	591.2	86.1
0°-40°	652.3	94.9
0°-60°	678.4	98.7
0°-90°	687.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	687.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2010	
5°	1868	166
15°	985	271
25°	327	155
35°	93	61
45°	22	19
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264633

CATALOG NUMBER: P3A09R259730DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2009.7
1°	2005.7
2°	1989.3
3°	1960.4
4°	1920.4
5°	1867.9
6°	1806.2
7°	1736.6
8°	1655.8
9°	1573.1
10°	1479.2
11°	1386.6
12°	1284.9
13°	1184.4
14°	1081.3
15°	984.8
17.5°	763.6
20°	579.7
22.5°	435.3
25°	327.0
27.5°	242.3
30°	177.9
32.5°	128.7
35°	92.6
37.5°	65.7
40°	46.0
42.5°	31.5
45°	22.3
47.5°	15.8
50°	11.8
52.5°	9.2
55°	7.9
57.5°	7.2
60°	5.9
62.5°	5.3
65°	5.3
67.5°	4.6
70°	3.9
72.5°	3.3
75°	2.6
77.5°	2.0
80°	1.3
82.5°	1.3
85°	0.7
87.5°	0.7



TEST NUMBER: P1264633

CATALOG NUMBER: P3A09R259730DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)