

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265082

Luminaire Tested: P3A13R359730DE010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265082  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R359730DE010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1107.0 lumens  
Efficiency: N/A  
Efficacy: 75.8 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265082  
CATALOG NUMBER: P3A13R359730DE010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1265082

CATALOG NUMBER: P3A13R359730DE010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	721828
5°	707130
10°	657859
15°	482296
20°	246958
25°	89013
30°	34664
35°	12126
40°	4981
45°	1364
50°	1194
55°	1338
60°	1140
65°	882
70°	1090
75°	1440
80°	1137
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 1512 cd/sqm



TEST NUMBER: P1265082  
 CATALOG NUMBER: P3A13R359730DE010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	299.5	27.1
10°-20°	561.9	50.8
20°-30°	198.9	18.0
30°-40°	34.8	3.1
40°-50°	5.1	0.5
50°-60°	2.8	0.3
60°-70°	2.0	0.2
70°-80°	1.5	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1060.3	95.8
0°-40°	1095.2	98.9
0°-60°	1103.1	99.7
0°-90°	1107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1107.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3292	
5°	3212	299
15°	2124	562
25°	368	199
35°	45	35
45°	4	5
55°	4	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1265082  
CATALOG NUMBER: P3A13R359730DE010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3291.8
1°	3291.0
2°	3280.5
3°	3260.5
4°	3242.1
5°	3212.5
6°	3182.0
7°	3148.0
8°	3106.2
9°	3040.8
10°	2954.5
11°	2835.0
12°	2691.2
13°	2520.3
14°	2332.0
15°	2124.5
17.5°	1582.3
20°	1058.3
22.5°	638.1
25°	367.9
27.5°	219.7
30°	136.9
32.5°	79.3
35°	45.3
37.5°	28.8
40°	17.4
42.5°	8.7
45°	4.4
47.5°	3.5
50°	3.5
52.5°	3.5
55°	3.5
57.5°	2.6
60°	2.6
62.5°	2.6
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0



TEST NUMBER: P1265082  
CATALOG NUMBER: P3A13R359730DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)