

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264641

Luminaire Tested: P3A09R309730DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R309730DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 835.1 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264641
CATALOG NUMBER: P3A09R309730DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1264641
 CATALOG NUMBER: P3A09R309730DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	96	95
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	92
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	89	86	84
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	679967
5°	667113
10°	590570
15°	374168
20°	142019
25°	42051
30°	16610
35°	5086
40°	2261
45°	806
50°	682
55°	497
60°	570
65°	675
70°	449
75°	593
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 80°
 Luminance: 884 cd/sqm



TEST NUMBER: P1264641
 CATALOG NUMBER: P3A09R309730DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	278.6	33.4
10°-20°	434.2	52.0
20°-30°	100.8	12.1
30°-40°	15.6	1.9
40°-50°	2.7	0.3
50°-60°	1.2	0.1
60°-70°	1.1	0.1
70°-80°	0.7	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	813.6	97.4
0°-40°	829.2	99.3
0°-60°	833.2	99.8
0°-90°	835.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	835.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3101	
5°	3031	279
15°	1648	434
25°	174	101
35°	19	16
45°	3	3
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1264641
CATALOG NUMBER: P3A09R309730DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3100.9
1°	3099.0
2°	3090.4
3°	3076.0
4°	3057.6
5°	3030.7
6°	2997.3
7°	2947.4
8°	2879.2
9°	2778.9
10°	2652.3
11°	2489.0
12°	2304.7
13°	2100.1
14°	1875.1
15°	1648.2
17.5°	1078.2
20°	608.6
22.5°	310.9
25°	173.8
27.5°	106.9
30°	65.6
32.5°	35.4
35°	19.0
37.5°	12.5
40°	7.9
42.5°	4.6
45°	2.6
47.5°	2.0
50°	2.0
52.5°	1.3
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1264641
CATALOG NUMBER: P3A09R309730DE010 E3CD1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)