

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265128

Luminaire Tested: P3A13R409730DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409730DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 778.9 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265128
CATALOG NUMBER: P3A13R409730DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1265128
 CATALOG NUMBER: P3A13R409730DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174876
5°	171692
10°	161854
15°	147016
20°	129138
25°	110281
30°	91356
35°	70457
40°	50151
45°	33771
50°	18422
55°	12998
60°	12236
65°	11311
70°	10066
75°	9574
80°	7703
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33771 cd/sqm



TEST NUMBER: P1265128
 CATALOG NUMBER: P3A13R409730DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	9.3
10°-20°	180.4	23.2
20°-30°	208.5	26.8
30°-40°	164.3	21.1
40°-50°	84.3	10.8
50°-60°	32.2	4.1
60°-70°	21.3	2.7
70°-80°	11.6	1.5
80°-90°	3.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.7	59.3
0°-40°	626.0	80.4
0°-60°	742.6	95.3
0°-90°	778.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	798	
5°	780	73
15°	648	180
25°	456	209
35°	263	164
45°	109	84
55°	34	32
65°	22	21
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P1265128
CATALOG NUMBER: P3A13R409730DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	797.5
2.5°	793.1
5°	780.0
7.5°	757.4
10°	726.9
12.5°	691.1
15°	647.6
17.5°	602.2
20°	553.4
22.5°	503.8
25°	455.8
27.5°	407.9
30°	360.8
32.5°	312.9
35°	263.2
37.5°	217.0
40°	175.2
42.5°	139.4
45°	108.9
47.5°	79.3
50°	54.0
52.5°	39.2
55°	34.0
57.5°	30.5
60°	27.9
62.5°	24.4
65°	21.8
67.5°	18.3
70°	15.7
72.5°	13.1
75°	11.3
77.5°	8.7
80°	6.1
82.5°	5.2
85°	2.6
87.5°	1.7
90°	0.0

(END OF REPORT)