

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264744

Luminaire Tested: P3A09R459730DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R459730DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 569.0 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264744
CATALOG NUMBER: P3A09R459730DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1264744

CATALOG NUMBER: P3A09R459730DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120648
5°	118512
10°	112133
15°	102271
20°	90425
25°	78537
30°	67403
35°	56162
40°	41850
45°	25615
50°	11872
55°	9290
60°	8903
65°	8146
70°	7565
75°	7202
80°	6566
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25615 cd/sqm



TEST NUMBER: P1264744
 CATALOG NUMBER: P3A09R459730DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	8.8
10°-20°	125.4	22.0
20°-30°	149.0	26.2
30°-40°	129.5	22.8
40°-50°	64.9	11.4
50°-60°	22.6	4.0
60°-70°	15.8	2.8
70°-80°	8.8	1.5
80°-90°	2.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.7	57.1
0°-40°	454.2	79.8
0°-60°	541.7	95.2
0°-90°	569.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	569.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	550	
5°	538	50
15°	450	125
25°	325	149
35°	210	129
45°	83	65
55°	24	23
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1264744
CATALOG NUMBER: P3A09R459730DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	550.2
2.5°	547.5
5°	538.4
7.5°	523.9
10°	503.6
12.5°	478.7
15°	450.5
17.5°	419.0
20°	387.5
22.5°	355.4
25°	324.6
27.5°	295.1
30°	266.2
32.5°	238.7
35°	209.8
37.5°	179.0
40°	146.2
42.5°	114.1
45°	82.6
47.5°	54.4
50°	34.8
52.5°	26.9
55°	24.3
57.5°	22.3
60°	20.3
62.5°	18.4
65°	15.7
67.5°	13.8
70°	11.8
72.5°	9.8
75°	8.5
77.5°	6.6
80°	5.2
82.5°	3.9
85°	2.0
87.5°	1.3
90°	0.0

(END OF REPORT)