

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265189

Luminaire Tested: P3A13R509730DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R509730DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 643.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265189
CATALOG NUMBER: P3A13R509730DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265189
 CATALOG NUMBER: P3A13R509730DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.6	11.9
10°-20°	180.0	28.0
20°-30°	184.2	28.6
30°-40°	116.8	18.2
40°-50°	46.5	7.2
50°-60°	18.8	2.9
60°-70°	12.0	1.9
70°-80°	6.2	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	440.8	68.5
0°-40°	557.6	86.7
0°-60°	622.9	96.9
0°-90°	643.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	643.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	827	77
15°	650	180
25°	405	184
35°	184	117
45°	57	46
55°	21	19
65°	12	12
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1265189

CATALOG NUMBER: P3A13R509730DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	852.9
2.5°	846.8
5°	826.7
7.5°	795.4
10°	753.6
12.5°	704.0
15°	650.1
17.5°	590.9
20°	529.1
22.5°	467.3
25°	404.7
27.5°	342.0
30°	283.7
32.5°	231.5
35°	184.5
37.5°	144.5
40°	109.7
42.5°	80.9
45°	56.6
47.5°	38.3
50°	27.8
52.5°	23.5
55°	20.9
57.5°	18.3
60°	15.7
62.5°	13.9
65°	12.2
67.5°	10.4
70°	8.7
72.5°	7.0
75°	6.1
77.5°	4.4
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)