

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265415

Luminaire Tested: P3A17R309730DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R309730DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 941.0 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265415
CATALOG NUMBER: P3A17R309730DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265415
 CATALOG NUMBER: P3A17R309730DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	9.7
10°-20°	220.2	23.4
20°-30°	248.2	26.4
30°-40°	198.2	21.1
40°-50°	101.8	10.8
50°-60°	38.3	4.1
60°-70°	25.1	2.7
70°-80°	13.6	1.4
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.0	59.5
0°-40°	758.2	80.6
0°-60°	898.4	95.5
0°-90°	941.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	941.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1014	
5°	987	92
15°	792	220
25°	542	248
35°	319	198
45°	129	102
55°	39	38
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1265415
CATALOG NUMBER: P3A17R309730DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1013.8
1°	1013.8
2°	1010.4
3°	1004.6
4°	996.5
5°	987.3
6°	975.7
7°	960.7
8°	944.5
9°	926.1
10°	907.6
11°	886.8
12°	864.9
13°	841.8
14°	817.5
15°	792.1
17.5°	727.5
20°	662.8
22.5°	600.4
25°	541.6
27.5°	483.8
30°	429.5
32.5°	374.1
35°	318.7
37.5°	264.4
40°	213.6
42.5°	168.6
45°	129.3
47.5°	95.8
50°	67.0
52.5°	47.3
55°	39.3
57.5°	35.8
60°	32.3
62.5°	28.9
65°	25.4
67.5°	21.9
70°	18.5
72.5°	15.0
75°	12.7
77.5°	10.4
80°	8.1
82.5°	5.8
85°	3.5
87.5°	1.2



TEST NUMBER: P1265415
CATALOG NUMBER: P3A17R309730DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)