

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265501

Luminaire Tested: P3A17R459730DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265501  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R459730DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1001.9 lumens  
Efficiency: N/A  
Efficacy: 47.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265501

CATALOG NUMBER: P3A17R459730DE010 E3DLD1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1265501

CATALOG NUMBER: P3A17R459730DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 96  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 82  | 97  | 90  | 85  | 81  | 88  | 83  | 80  |  | 85  | 81  | 78  |  | 83  |
| 4   | 94  | 85  | 78  | 74  | 92  | 84  | 78  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 79  | 72  | 67  | 86  | 78  | 71  | 67  | 76  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 66  | 61  | 71  | 65  | 61  |  | 69  | 64  | 60  |  | 68  |
| 7   | 78  | 68  | 61  | 57  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 65  | 60  | 56  |  | 64  |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  |
| 9   | 70  | 60  | 53  | 49  | 69  | 59  | 53  | 49  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 67  | 56  | 50  | 45  | 66  | 56  | 49  | 45  | 55  | 49  | 45  |  | 54  | 49  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 212439 |
| 5°  | 208672 |
| 10° | 197458 |
| 15° | 180092 |
| 20° | 159264 |
| 25° | 138298 |
| 30° | 118702 |
| 35° | 98912  |
| 40° | 73710  |
| 45° | 45121  |
| 50° | 20878  |
| 55° | 16324  |
| 60° | 15700  |
| 65° | 14372  |
| 70° | 13336  |
| 75° | 12709  |
| 80° | 11618  |
| 85° | 8806   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45121 cd/sqm

TEST NUMBER: P1265501

CATALOG NUMBER: P3A17R459730DE010 E3DLD1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 88.6   | 8.8       |
| 10°-20°   | 220.9  | 22.0      |
| 20°-30°   | 262.4  | 26.2      |
| 30°-40°   | 228.0  | 22.8      |
| 40°-50°   | 114.3  | 11.4      |
| 50°-60°   | 39.7   | 4.0       |
| 60°-70°   | 27.8   | 2.8       |
| 70°-80°   | 15.5   | 1.5       |
| 80°-90°   | 4.7    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 571.9  | 57.1      |
| 0°-40°    | 799.9  | 79.8      |
| 0°-60°    | 953.9  | 95.2      |
| 0°-90°    | 1001.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1001.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 969 |      |
| 5°  | 948 | 89   |
| 15° | 793 | 221  |
| 25° | 572 | 262  |
| 35° | 370 | 228  |
| 45° | 146 | 114  |
| 55° | 43  | 40   |
| 65° | 28  | 28   |
| 75° | 15  | 16   |
| 85° | 4   | 5    |
| 90° | 0   |      |

TEST NUMBER: P1265501

CATALOG NUMBER: P3A17R459730DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 968.8 |
| 2.5°  | 964.2 |
| 5°    | 948.0 |
| 7.5°  | 922.6 |
| 10°   | 886.8 |
| 12.5° | 843.0 |
| 15°   | 793.3 |
| 17.5° | 737.9 |
| 20°   | 682.5 |
| 22.5° | 625.9 |
| 25°   | 571.6 |
| 27.5° | 519.6 |
| 30°   | 468.8 |
| 32.5° | 420.3 |
| 35°   | 369.5 |
| 37.5° | 315.2 |
| 40°   | 257.5 |
| 42.5° | 200.9 |
| 45°   | 145.5 |
| 47.5° | 95.8  |
| 50°   | 61.2  |
| 52.5° | 47.3  |
| 55°   | 42.7  |
| 57.5° | 39.3  |
| 60°   | 35.8  |
| 62.5° | 32.3  |
| 65°   | 27.7  |
| 67.5° | 24.2  |
| 70°   | 20.8  |
| 72.5° | 17.3  |
| 75°   | 15.0  |
| 77.5° | 11.5  |
| 80°   | 9.2   |
| 82.5° | 6.9   |
| 85°   | 3.5   |
| 87.5° | 2.3   |
| 90°   | 0.0   |

(END OF REPORT)