

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265507

Luminaire Tested: P3A17R459730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R459730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 833.0 lumens
Efficiency: N/A
Efficacy: 39.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265507
CATALOG NUMBER: P3A17R459730DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1265507
 CATALOG NUMBER: P3A17R459730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248116
5°	242460
10°	223665
15°	194485
20°	159777
25°	124314
30°	91786
35°	64594
40°	40333
45°	21832
50°	11803
55°	10169
60°	9122
65°	7783
70°	6668
75°	6863
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21832 cd/sqm



TEST NUMBER: P1265507
 CATALOG NUMBER: P3A17R459730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	12.2
10°-20°	236.8	28.4
20°-30°	235.1	28.2
30°-40°	151.4	18.2
40°-50°	58.3	7.0
50°-60°	23.7	2.8
60°-70°	15.0	1.8
70°-80°	8.1	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.0	68.9
0°-40°	725.4	87.1
0°-60°	807.4	96.9
0°-90°	833.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1132	
5°	1102	102
15°	857	237
25°	514	235
35°	241	151
45°	70	58
55°	27	24
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1265507
CATALOG NUMBER: P3A17R459730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1131.5
2.5°	1125.7
5°	1101.5
7.5°	1059.9
10°	1004.5
12.5°	935.2
15°	856.7
17.5°	771.3
20°	684.7
22.5°	596.9
25°	513.8
27.5°	435.3
30°	362.5
32.5°	299.0
35°	241.3
37.5°	189.4
40°	140.9
42.5°	101.6
45°	70.4
47.5°	47.3
50°	34.6
52.5°	28.9
55°	26.6
57.5°	23.1
60°	20.8
62.5°	17.3
65°	15.0
67.5°	12.7
70°	10.4
72.5°	9.2
75°	8.1
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)