

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265556

Luminaire Tested: P3A17R559730DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R559730DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 977.0 lumens
Efficiency: N/A
Efficacy: 46.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265556
CATALOG NUMBER: P3A17R559730DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1265556
 CATALOG NUMBER: P3A17R559730DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183691
5°	181355
10°	174212
15°	162929
20°	148646
25°	132612
30°	115993
35°	96369
40°	75971
45°	51540
50°	31487
55°	16324
60°	15174
65°	14372
70°	13336
75°	11692
80°	11618
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 51540 cd/sqm



TEST NUMBER: P1265556
 CATALOG NUMBER: P3A17R559730DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	7.9
10°-20°	200.6	20.5
20°-30°	251.2	25.7
30°-40°	224.2	23.0
40°-50°	131.3	13.4
50°-60°	45.4	4.6
60°-70°	27.4	2.8
70°-80°	15.2	1.6
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.1	54.2
0°-40°	753.3	77.1
0°-60°	930.0	95.2
0°-90°	977.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	977.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	838	
5°	824	77
15°	718	201
25°	548	251
35°	360	224
45°	166	131
55°	43	45
65°	28	27
75°	14	15
85°	4	4
90°	0	



TEST NUMBER: P1265556
CATALOG NUMBER: P3A17R559730DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	837.7
2.5°	833.1
5°	823.9
7.5°	805.4
10°	782.4
12.5°	753.5
15°	717.7
17.5°	679.7
20°	637.0
22.5°	593.1
25°	548.1
27.5°	503.1
30°	458.1
32.5°	409.6
35°	360.0
37.5°	311.6
40°	265.4
42.5°	215.8
45°	166.2
47.5°	126.9
50°	92.3
52.5°	60.0
55°	42.7
57.5°	38.1
60°	34.6
62.5°	31.2
65°	27.7
67.5°	24.2
70°	20.8
72.5°	17.3
75°	13.8
77.5°	11.5
80°	9.2
82.5°	5.8
85°	3.5
87.5°	2.3
90°	0.0

(END OF REPORT)