

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265573

Luminaire Tested: P3A17R609730DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R609730DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1383.0 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265573
CATALOG NUMBER: P3A17R609730DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1265573
 CATALOG NUMBER: P3A17R609730DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362361
5°	342086
10°	333194
15°	325564
20°	302706
25°	270620
30°	206715
35°	119337
40°	46315
45°	19289
50°	4230
55°	650
60°	482
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19289 cd/sqm



TEST NUMBER: P1265573
 CATALOG NUMBER: P3A17R609730DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	10.6
10°-20°	399.5	28.9
20°-30°	500.4	36.2
30°-40°	279.7	20.2
40°-50°	53.1	3.8
50°-60°	2.7	0.2
60°-70°	0.7	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.6	75.7
0°-40°	1326.3	95.9
0°-60°	1382.1	99.9
0°-90°	1383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1652	
5°	1554	147
15°	1434	399
25°	1118	500
35°	446	280
45°	62	53
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1265573
CATALOG NUMBER: P3A17R609730DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1652.5
1°	1645.7
2°	1624.2
3°	1598.8
4°	1575.0
5°	1554.1
6°	1538.2
7°	1524.7
8°	1514.5
9°	1504.9
10°	1496.4
11°	1487.9
12°	1478.3
13°	1466.4
14°	1452.2
15°	1434.1
16°	1412.1
17°	1387.2
18°	1358.9
19°	1326.7
20°	1297.2
21°	1265.6
22°	1232.7
23°	1198.2
24°	1160.3
25°	1118.5
26°	1069.2
27°	1014.4
28°	952.7
29°	887.1
30°	816.4
31°	745.1
32°	671.5
32.5°	631.4
33°	595.2
34°	519.9
35°	445.8
36°	379.0
37°	308.3
37.5°	276.1
38°	244.4
39°	196.9
40°	161.8
42.5°	98.4
45°	62.2

TEST NUMBER: P1265573
CATALOG NUMBER: P3A17R609730DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	34.5
50°	12.4
52.5°	2.8
55°	1.7
57.5°	1.1
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)