

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265597

Luminaire Tested: P3A17R659730DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R659730DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1428.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265597
CATALOG NUMBER: P3A17R659730DE010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265597
 CATALOG NUMBER: P3A17R659730DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			93
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75			75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	348963
5°	328439
10°	324265
15°	318549
20°	300769
25°	279137
30°	216970
35°	125521
40°	50580
45°	23289
50°	9074
55°	3517
60°	3026
65°	3009
70°	2949
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23289 cd/sqm



TEST NUMBER: P1265597
 CATALOG NUMBER: P3A17R659730DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.8	9.9
10°-20°	391.8	27.4
20°-30°	512.9	35.9
30°-40°	297.1	20.8
40°-50°	63.6	4.5
50°-60°	10.4	0.7
60°-70°	5.7	0.4
70°-80°	3.4	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.6	73.3
0°-40°	1343.7	94.1
0°-60°	1417.7	99.3
0°-90°	1428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1428.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1591	
5°	1492	142
15°	1403	392
25°	1154	513
35°	469	297
45°	75	64
55°	9	10
65°	6	6
75°	4	3
85°	1	1
90°	0	



TEST NUMBER: P1265597
CATALOG NUMBER: P3A17R659730DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1591.4
2.5°	1546.4
5°	1492.1
7.5°	1470.2
10°	1456.3
12.5°	1436.7
15°	1403.2
17.5°	1351.2
20°	1288.9
22.5°	1230.0
25°	1153.7
27.5°	1025.5
30°	856.9
32.5°	664.1
35°	468.9
37.5°	296.8
40°	176.7
42.5°	110.9
45°	75.1
47.5°	48.5
50°	26.6
52.5°	12.7
55°	9.2
57.5°	8.1
60°	6.9
62.5°	6.9
65°	5.8
67.5°	4.6
70°	4.6
72.5°	3.5
75°	3.5
77.5°	2.3
80°	2.3
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)