

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265798

Luminaire Tested: P3A20R309730D010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265798  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R309730D010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 976.9 lumens  
Efficiency: N/A  
Efficacy: 33.9 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265798

CATALOG NUMBER: P3A20R309730D010 E3DLP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1265798

CATALOG NUMBER: P3A20R309730D010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 84  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 83  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 63  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 60  | 57  | 65  | 60  | 56  |  | 64  | 60  | 56  |  | 63  |
| 10  | 73  | 63  | 58  | 54  | 72  | 63  | 57  | 54  | 62  | 57  | 54  |  | 61  | 57  | 53  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 333855 |
| 5°  | 323464 |
| 10° | 291444 |
| 15° | 241091 |
| 20° | 186660 |
| 25° | 140016 |
| 30° | 101661 |
| 35° | 67726  |
| 40° | 41621  |
| 45° | 24437  |
| 50° | 14976  |
| 55° | 12157  |
| 60° | 10613  |
| 65° | 8665   |
| 70° | 7758   |
| 75° | 7710   |
| 80° | 5683   |
| 85° | 7548   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24437 cd/sqm

TEST NUMBER: P1265798

CATALOG NUMBER: P3A20R309730D010 E3DLP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 135.2  | 13.8      |
| 10°-20°   | 292.5  | 29.9      |
| 20°-30°   | 266.1  | 27.2      |
| 30°-40°   | 160.9  | 16.5      |
| 40°-50°   | 64.5   | 6.6       |
| 50°-60°   | 28.5   | 2.9       |
| 60°-70°   | 17.2   | 1.8       |
| 70°-80°   | 9.4    | 1.0       |
| 80°-90°   | 2.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 693.7  | 71.0      |
| 0°-40°    | 854.6  | 87.5      |
| 0°-60°    | 947.7  | 97.0      |
| 0°-90°    | 976.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 976.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1522 |      |
| 5°  | 1470 | 135  |
| 15° | 1062 | 292  |
| 25° | 579  | 266  |
| 35° | 253  | 161  |
| 45° | 79   | 65   |
| 55° | 32   | 29   |
| 65° | 17   | 17   |
| 75° | 9    | 9    |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1265798

CATALOG NUMBER: P3A20R309730D010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1522.5 |
| 1°    | 1521.0 |
| 2°    | 1514.9 |
| 3°    | 1504.3 |
| 4°    | 1489.2 |
| 5°    | 1469.5 |
| 6°    | 1445.3 |
| 7°    | 1419.5 |
| 8°    | 1386.2 |
| 9°    | 1348.3 |
| 10°   | 1308.9 |
| 11°   | 1263.5 |
| 12°   | 1215.0 |
| 13°   | 1166.5 |
| 14°   | 1113.5 |
| 15°   | 1062.0 |
| 17.5° | 927.1  |
| 20°   | 799.9  |
| 22.5° | 681.7  |
| 25°   | 578.7  |
| 27.5° | 484.8  |
| 30°   | 401.5  |
| 32.5° | 324.2  |
| 35°   | 253.0  |
| 37.5° | 193.9  |
| 40°   | 145.4  |
| 42.5° | 106.0  |
| 45°   | 78.8   |
| 47.5° | 59.1   |
| 50°   | 43.9   |
| 52.5° | 34.8   |
| 55°   | 31.8   |
| 57.5° | 27.3   |
| 60°   | 24.2   |
| 62.5° | 19.7   |
| 65°   | 16.7   |
| 67.5° | 15.1   |
| 70°   | 12.1   |
| 72.5° | 10.6   |
| 75°   | 9.1    |
| 77.5° | 7.6    |
| 80°   | 4.5    |
| 82.5° | 3.0    |
| 85°   | 3.0    |
| 87.5° | 1.5    |



TEST NUMBER: P1265798

CATALOG NUMBER: P3A20R309730D010 E3DLP1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)