

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267500

Luminaire Tested: P3A13R409735DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409735DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1055.0 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267500
CATALOG NUMBER: P3A13R409735DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1267500
 CATALOG NUMBER: P3A13R409735DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94	94	94	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63	63	63	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60	60	60	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	466827
5°	453268
10°	411326
15°	339820
20°	245115
25°	151606
30°	82089
35°	42429
40°	23072
45°	12932
50°	6482
55°	4855
60°	4386
65°	4203
70°	4039
75°	3813
80°	3410
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12932 cd/sqm



TEST NUMBER: P1267500
 CATALOG NUMBER: P3A13R409735DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.8	18.0
10°-20°	407.6	38.6
20°-30°	290.9	27.6
30°-40°	107.1	10.2
40°-50°	33.7	3.2
50°-60°	11.7	1.1
60°-70°	8.1	0.8
70°-80°	4.7	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.3	84.2
0°-40°	995.4	94.3
0°-60°	1040.8	98.7
0°-90°	1055.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1055.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2129	
5°	2059	190
15°	1497	408
25°	627	291
35°	158	107
45°	42	34
55°	13	12
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1267500
CATALOG NUMBER: P3A13R409735DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2128.9
2.5°	2112.6
5°	2059.2
7.5°	1970.4
10°	1847.3
12.5°	1690.6
15°	1496.9
17.5°	1279.5
20°	1050.4
22.5°	824.9
25°	626.6
27.5°	460.0
30°	324.2
32.5°	227.3
35°	158.5
37.5°	112.3
40°	80.6
42.5°	58.0
45°	41.7
47.5°	28.1
50°	19.0
52.5°	13.6
55°	12.7
57.5°	11.8
60°	10.0
62.5°	9.1
65°	8.1
67.5°	7.2
70°	6.3
72.5°	5.4
75°	4.5
77.5°	3.6
80°	2.7
82.5°	1.8
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)