

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267661

Luminaire Tested: P3A13R709735DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R709735DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1132.9 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267661
CATALOG NUMBER: P3A13R709735DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1267661
 CATALOG NUMBER: P3A13R709735DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78				78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53				53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49				49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224982
5°	214681
10°	204249
15°	198798
20°	191443
25°	181196
30°	168532
35°	141556
40°	91257
45°	42392
50°	11121
55°	2753
60°	2763
65°	2335
70°	2308
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42392 cd/sqm



TEST NUMBER: P1267661
 CATALOG NUMBER: P3A13R709735DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.3	8.1
10°-20°	246.0	21.7
20°-30°	343.8	30.3
30°-40°	318.7	28.1
40°-50°	114.3	10.1
50°-60°	9.7	0.9
60°-70°	4.8	0.4
70°-80°	3.1	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.1	60.1
0°-40°	999.9	88.3
0°-60°	1123.8	99.2
0°-90°	1132.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1026	
5°	975	91
15°	876	246
25°	749	344
35°	529	319
45°	137	114
55°	7	10
65°	4	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1267661
CATALOG NUMBER: P3A13R709735DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1026.0
2.5°	1010.6
5°	975.3
7.5°	942.7
10°	917.3
12.5°	896.5
15°	875.7
17.5°	850.3
20°	820.4
22.5°	786.0
25°	748.9
27.5°	710.9
30°	665.6
32.5°	607.6
35°	528.8
37.5°	428.3
40°	318.8
42.5°	217.3
45°	136.7
47.5°	76.1
50°	32.6
52.5°	10.9
55°	7.2
57.5°	6.3
60°	6.3
62.5°	5.4
65°	4.5
67.5°	4.5
70°	3.6
72.5°	3.6
75°	2.7
77.5°	2.7
80°	1.8
82.5°	1.8
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)