

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265869

Luminaire Tested: P3A20R459730D010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265869  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R459730D010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1694.0 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265869  
CATALOG NUMBER: P3A20R459730D010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1265869  
 CATALOG NUMBER: P3A20R459730D010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	636155
5°	621240
10°	571087
15°	483885
20°	375443
25°	262443
30°	165317
35°	97333
40°	55075
45°	26793
50°	9313
55°	7531
60°	7324
65°	7057
70°	6796
75°	6439
80°	5683
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26793 cd/sqm



TEST NUMBER: P1265869  
 CATALOG NUMBER: P3A20R459730D010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.3	15.4
10°-20°	585.3	34.6
20°-30°	497.0	29.3
30°-40°	237.1	14.0
40°-50°	71.4	4.2
50°-60°	18.1	1.1
60°-70°	13.5	0.8
70°-80°	8.0	0.5
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1343.6	79.3
0°-40°	1580.7	93.3
0°-60°	1670.3	98.6
0°-90°	1694.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1694.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2901	
5°	2822	261
15°	2132	585
25°	1085	497
35°	364	237
45°	86	71
55°	20	18
65°	14	13
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1265869  
CATALOG NUMBER: P3A20R459730D010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2901.1
2.5°	2882.9
5°	2822.3
7.5°	2717.8
10°	2564.8
12.5°	2361.8
15°	2131.5
17.5°	1875.5
20°	1608.9
22.5°	1337.7
25°	1084.7
27.5°	854.4
30°	652.9
32.5°	490.8
35°	363.6
37.5°	268.1
40°	192.4
42.5°	133.3
45°	86.4
47.5°	48.5
50°	27.3
52.5°	21.2
55°	19.7
57.5°	18.2
60°	16.7
62.5°	15.1
65°	13.6
67.5°	12.1
70°	10.6
72.5°	9.1
75°	7.6
77.5°	6.1
80°	4.5
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)