

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267712

Luminaire Tested: P3A17R159735DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R159735DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1024.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267712

CATALOG NUMBER: P3A17R159735DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267712

CATALOG NUMBER: P3A17R159735DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101
2	113	110	108	106	111	109	107	105	106	104	103		103	102	100		100
3	111	107	104	102	109	106	103	101	104	101	100		101	100	98		99
4	109	104	101	99	107	103	101	99	102	99	98		100	98	97		98
5	107	102	99	97	105	101	99	96	100	97	96		99	96	95		97
6	105	100	97	95	104	100	97	95	98	96	94		97	95	93		96
7	103	98	95	93	102	98	95	93	97	94	93		96	94	92		95
8	101	97	94	92	101	96	94	92	96	93	91		95	93	91		94
9	100	95	92	90	99	95	92	90	94	92	90		94	91	90		93
10	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2159038
5°	1871930
10°	910159
15°	194167
20°	40814
25°	12146
30°	2633
35°	455
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1267712

CATALOG NUMBER: P3A17R159735DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	664.3	64.9
10°-20°	330.3	32.3
20°-30°	27.6	2.7
30°-40°	1.8	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1022.2	99.8
0°-40°	1024.0	100.0
0°-60°	1024.0	100.0
0°-90°	1024.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1024.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9846	
5°	8504	664
15°	855	330
25°	50	28
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267712

CATALOG NUMBER: P3A17R159735DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9846.0
2.5°	9501.5
5°	8504.2
7.5°	6511.5
10°	4087.6
12.5°	1966.8
15°	855.3
17.5°	436.3
20°	174.9
22.5°	86.6
25°	50.2
27.5°	26.0
30°	10.4
32.5°	3.5
35°	1.7
37.5°	1.7
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)