

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267736

Luminaire Tested: P3A17R209735DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267736  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R209735DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 944.1 lumens  
Efficiency: N/A  
Efficacy: 44.5 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267736  
CATALOG NUMBER: P3A17R209735DE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1267736

CATALOG NUMBER: P3A17R209735DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	233490
5°	227272
10°	209059
15°	184019
20°	157817
25°	132588
30°	107181
35°	81539
40°	58023
45°	38299
50°	23743
55°	15598
60°	14209
65°	13075
70°	12310
75°	11184
80°	10607
85°	9057

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 38299 cd/sqm



TEST NUMBER: P1267736  
 CATALOG NUMBER: P3A17R209735DE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	10.1
10°-20°	225.7	23.9
20°-30°	250.5	26.5
30°-40°	191.1	20.2
40°-50°	97.9	10.4
50°-60°	40.2	4.3
60°-70°	25.1	2.7
70°-80°	14.1	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.7	60.6
0°-40°	762.8	80.8
0°-60°	900.8	95.4
0°-90°	944.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1065	
5°	1032	96
15°	811	226
25°	548	250
35°	305	191
45°	124	98
55°	41	40
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1267736  
CATALOG NUMBER: P3A17R209735DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1064.8
1°	1066.0
2°	1061.2
3°	1055.2
4°	1045.7
5°	1032.5
6°	1016.9
7°	1000.1
8°	982.1
9°	960.5
10°	938.9
12.5°	876.6
15°	810.6
17.5°	743.5
20°	676.3
22.5°	609.2
25°	548.0
27.5°	486.9
30°	423.3
32.5°	363.3
35°	304.6
37.5°	253.0
40°	202.7
42.5°	159.5
45°	123.5
47.5°	93.5
50°	69.6
52.5°	51.6
55°	40.8
57.5°	37.2
60°	32.4
62.5°	28.8
65°	25.2
67.5°	21.6
70°	19.2
72.5°	15.6
75°	13.2
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)